

Ultrasound Bath Elmasonic S60H





- Materials surface cleaning for electrochemical deposition process
- Preparation disperse solutions
- Homogenization electrolytes
- The dispersion of nano and micro particles

Further advantages:

- high-performance 37 kHz sandwich transducer systems
- cleaning tank made of cavitation-resistant stainless steel
- user-friendly and clear operating panel, splash water proof
- LED-Display showing set and remaining time of cleaning period
- Turning knob for setting continued and short-period operation fr om 1 to 30 min
- temperature-controlled ultrasonic operation (applies only for units with heating)
- sweep function for an optimised sound field distribution in t he cleaning liquid by frequency modulation
- degas function for the efficient degassing of the cleaning liquid and for laboratory pur poses
- auto degas function for automatic degassing cycles, i.e. with fresh cleaning liquids
- dry-run protected heating (applies only for units with heatin g)
- LED-Display for pre-set and actual temperature (applies only for units with heating)
- plug-in mains supply (S 10 S 300H)
- ergonomically shaped plastic handles
- turning knob for tank drainage at side of unit for simple get ef fective draining of tank.